



SEEDBURO BARLEY OR WHEAT PEARLER

The Seedburo Barley Pearler is used to dehull barley for the determination of mellow-ness and heat-damaged kernels. It uses a 30 grit carborundum stone and a No. 7 mesh screen. The wheat pearler determines the hardness in wheat and comes with a 24 grit stone and a No. 8 mesh screen. The hulled (pearled) grain is discharged through the spout, while the chaff and hulls are passed through the screen into the catch drawer. Each unit is equipped with a ¼ HP motor and a 5 minute timing switch. Net wt. 35 lbs. Ship wt. 40 lbs. Dims. 20" L x 15" W x 12" H.

Barley Pearler, 110V, 60Hz	No. 109B/B
Barley Pearler, 220V, 50Hz	No. 109B/C
Barley Pearler, 220V, 60Hz	No. 109B/E
Wheat Pearler, 110V, 60Hz	No. 109W/B
Wheat Pearler, 220V, 50Hz	No. 109W/C
Wheat Pearler, 220V, 60Hz	No. 109W/E
Replacement Screen for Barley Pearler, 7 mesh	No. 109SB
Replacement Screen for Wheat Pearler, 8 mesh	No. 109SW
Replacement Stone for Barley Pearler, 30 grit	No. 109BS
Replacement Stone for Wheat Pearler, 24 grit	No. 109WS



SEEDBURO ELECTRIC SEED SCARIFIER

The Electric Sample Seed Scarifier is designed and built for convenient office or lab use on small sample seed lots. It features all steel construction for durability and long use. The processing drum is lined with caborundum and equipped with a rotating steel propeller for thorough and efficient scarification of your sample seeds. Electric motor 1/3 HP. Net wt. 30 lbs. Ship wt. 32lbs, Dims. 16" L x 12" W x 12" H.

Electric Seed Scarifier, 110V, 60Hz	No. 390/B
Electric Seed Scarifier, 220V, 50Hz	No. 390/C
Electric Seed Scarifier, 220V, 60Hz	No. 390/E



SEEDBURO PERGAMINO COFFEE SHELLER

The Seedburo Pergamino Coffee Sheller is a great aid in the inspection of samples in the coffee processing laboratory. In less than 5 minutes, a sample of 250g of pergamino coffee will be converted into oro (gold) coffee in order to determine quality and rendition. All contact parts in the sheller chamber are anti-corrosive material. Time (0-180 seconds), speed (0-1725 RPM) and shelling pressure are adjustable according to your needs. Electric motor ½ HP. Net wt. 49 lbs. Ship wt. 62 lbs. Dims. 22" L x 12½" W x 17" H.

Coffee Sheller, 110V, 50/60Hz	No. 60-M-250-115
Coffee Sheller, 220V, 50/60Hz	No. 60-M-250-220
Domestic Packing	No. 60M-BOX-C
Export Wooden Crate	No. 60M-BOX-W



SEEDBURO LABORATORY OAT HULLER

The Seedburo Oat Huller is designed to minimize breakage during hulling operation. Hulling a 50 gram sample takes approximately one minute. Hulls and fuzz are separated from the groats and are sorted into two separate collection canisters, allowing for quick weighing of fractions. The fractions allow the lab technician to check for heat and frost damage, mold, weathering, discoloration and odor. The unit's simple and rugged design nearly eliminates the need for spare parts. The unit comes complete with 1/3HP motor, 110/220V, 50/60Hz, 1PH. Net wt. 115 lbs. Ship wt. 370 lbs. Dims. 30" L x 38" W x 89" H.

Oat Huller, 110/220V, 50/60Hz	No. OH5095
-------------------------------------	-------------------